



Overview

Model Name	APC Smart-UPS XL Modular 3000VA 120V Rackmount/Tower
Includes	CD with software
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla

Output

Output Power Capacity	2850 Watts / 3000 VA
Max Configurable Power (Watts)	2850 Watts / 3000 VA
Nominal Output Voltage	120V
Nominal Output Voltage	Line Interactive
Output Connections	(2) NEMA 5-20R (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA L5-30P
Cord Length	3,05 meters
Input voltage range for main operations	82 - 147 V
Input voltage adjustable range for mains operation	75 - 154V

Batteries & Runtime

Battery Type	VRLA
Typical recharge time	3 hour(s)
Replacement Battery	RBC43
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-9 RS-232
-------------------	-------------

Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	540 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	86.0 mm
Maximum Width	432.0 mm
Maximum Depth	678.0 mm
Rack Height	2 U
Net Weight	46.82 kg
Shipping Weight	56.82 kg
Shipping Height	250.0 mm
Shipping Width	596.0 mm
Shipping Depth	980.0 mm
Color	Black
Units per Pallet	8.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 55 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	300.000 BTU/hr

Conformance

Approvals	BSMI
Standard warranty	2 years repair or replace
Equipment protection policy	Lifetime : \$150000