



Overview

Model Name	APC 3000VA Filter - MARINE
Includes	Installation guide
Standard Lead Time	Usually in Stock
Product Distribution	Albania

Output

Nominal Output Voltage	200V
Maximum Total Current Draw per Phase	16 A
Output Connections	(1) IEC 320 C19 (Battery Backup)
Always on Outlets	1
Overload Protection	No
Cord Length	8

Input

Nominal Input Voltage	208V
Input Frequency	47 - 63 Hz
Regulatory Derated Input Current (North America)	16 A
Input Connections	IEC-320 C20
Cord Length	2.44 meters
Number of Power Cords	1
Acceptable Input Voltage	100-240 VAC
Maximum Line Current per phase	16 A
Maximum Input Current per phase	16 A
Load Capacity	3000 VA

Physical

Net Weight	5.09 kg
Maximum Height	44.0 mm
Maximum Width	432.0 mm

Maximum Depth	279.0 mm
Shipping Weight	6.36 kg
Shipping Height	76.0 mm
Shipping Width	381.0 mm
Shipping Depth	559.0 mm
Color	Black

Environmental

Operating Environment	0 - 55 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 75 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	DNV
Standard warranty	2 years repair or replace
Equipment protection policy	--

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs