



Overview

Model Name	APC 6000VA Filter - Marine
Includes	Installation guide , Mounting Hardware , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Bulgaria , Burkina Faso , Burundi , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Namibia , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Output

Nominal Output Voltage	200V , 208V , 220V , 230V , 240V
Maximum Total Current Draw per Phase	32 A
Output Connections	(1) Hard Wire 3-wire (H N + G) (Battery Backup) , (2) Screw Terminals (Battery Backup)

Input

Nominal Input Voltage	200V , 208V , 220V , 230V , 240V
Input Frequency	45 - 65 Hz
Regulatory Derated Input Current (North America)	32 A

Input Connections	Hard Wire 3-wire
Acceptable Input Voltage	180-264 VAC
Maximum Line Current per phase	32 A
Maximum Input Current per phase	32 A
Load Capacity	6000 VA

Physical

Net Weight	6.73 kg
Maximum Height	44.0 mm
Maximum Width	483.0 mm
Maximum Depth	330.0 mm
Shipping Weight	8.27 kg
Shipping Height	76.0 mm
Shipping Width	559.0 mm
Shipping Depth	406.0 mm
Color	Black

Environmental

Operating Environment	0 - 55 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 75 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	DNV
Standard warranty	2 year (manufacturer's defect)

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs