



Overview

Model Name	APC SMART-UPS RT 5000VA 220V For Taiwan
Includes	CD with software
Standard Lead Time	Usually in Stock
Product Distribution	Taiwan

Output

Output Power Capacity	3500 Watts / 5000 VA
Max Configurable Power (Watts)	3500 Watts / 5000 VA
Nominal Output Voltage	220V
Output Voltage Distortion	Less than 3%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz user adjustable +/- 0.1
Other Output Voltages	208V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(2) NEMA L6-20R (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	220V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA L6-30P
Cord Length	3.05 meters
Input voltage range for main operations	160 - 280 V
Input voltage adjustable range for mains operation	100 - 280V
Other Input Voltages	208

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
--------------	--

Included Battery Modules	2
Typical recharge time	2.5 hour(s)
Replacement Battery	APCRBC140
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-25 RS-232
Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	432.0 mm
Maximum Width	130.0 mm
Maximum Depth	660.0 mm
Rack Height	3 U
Net Weight	54.56 kg
Shipping Weight	63.64 kg
Shipping Height	347.0 mm
Shipping Width	603.0 mm
Shipping Depth	980.0 mm
Master Carton Units	1.0
Color	Black
Units per Pallet	6.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	1040.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	BSMI
Standard warranty	2 years repair or replace