

# SUVT10KH4B4S

APC Smart-UPS Vt 10kVA 400V w/4 Batt. Modules, Start-Up 5X8, Internal Maintenance Bypass



SUVT10KH4B4S has not been replaced. Please contact your customer care center for more information.

## Overview

Model Name	APC Smart-UPS Vt 10kVA 400V w/4 Batt. Modules, Start-Up 5X8, Internal Maintenance Bypass
Includes	Battery modules ship installed , Bolt down brackets , CD with software , Installation guide , Power modules ship installed , Start up included , User Manual , Web/SNMP Management Card
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guatemala , Guinea , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

## Output

Output Power Capacity	8000 Watts / 10.0 kVA
Max Configurable Power (Watts)	8000 Watts / 10.0 kVA
Nominal Output Voltage	230V , 400 3PH
Output Voltage Note	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal
Other Output Voltages	380, 415V
Crest Factor	Unlimited
Crest Factor	Double Conversion Online
Waveform Type	Sine wave

Output Connections	(1) Hard Wire 4-wire (3PH + G) (Battery Backup) , (1) Hard Wire 5-wire (3PH + N + G) (Battery Backup) , (1) Screw Terminals (Battery Backup)
Bypass	Built-in Maintenance Bypass , Built-in Static Bypass

## Input

Nominal Input Voltage	400 3PH
Input Frequency	47 - 70 Hz (auto sensing)
Input Connections	Hard Wire 5-wire (3PH + N + G)
Input voltage range for main operations	304 - 477 V
Other Input Voltages	380 , 415
Maximum Input Current	14 A
Input Breaker Capacity	20 A

## Batteries & Runtime

Battery Type	VRLA
Included Battery Modules	4
Typical recharge time	5 hour(s)
Replacement Battery	SYBT4
RBC Quantity	4

## Communications & Management

Interface Port(s)	DB-9 RS-232 , Smart-Slot
Pre-Installed SmartSlot™ Cards	AP9619
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

## Physical

Maximum Height	1499.0 mm
Maximum Width	559.0 mm
Maximum Depth	813.0 mm
Net Weight	599.1 kg
Shipping Weight	630.0 kg
Shipping Height	1643.0 mm
Shipping Width	650.0 mm
Shipping Depth	1062.0 mm
Color	Black
Units per Pallet	1.0

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999.9 meters
Storage Temperature	-50 - 40 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	64.000 dB
Online Thermal Dissipation	1774.000 BTU/hr
Protection Class	IP 20

## Conformance

---

Approvals	C-tick , CE , EN 50091-2 , EN/IEC 62040-3 , IEC 61000-3-2 , IEC 61000-3-3 , ISO 14001 , ISO 9001 , VFI-SS-112
Standard warranty	1 year repair or replace , Start-Up Service

---