



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 6 port(s) copper cable 100BASE-FX - 3 port(s) fiber optic
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	Duplex SC fiber optic Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for fiber optic Multimode optical fiber for copper cable
Cable distance between devices	<= 100 m copper cable
Attenuation	11 dB 62.2/125 μm 8 dB 50/125 μm
Ethernet service	Configuration via web server Data stream control FDR IGMP Snooping Multicast filtering Priority port Rapid Scanning Tree Protocol (RSTP) Secure port SMTP V3 SNTP client
Maximum number of switches in a ring	50
Redundancy	Redundant power supplies Redundant single ring Ring coupling
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	9 W
Electrical connection	Removable connector 6 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local signalling	1 LED fault 2 LEDs P1 P2 power supplies 1 LED ring manager 1 LED stand-by 1 LED per channel copper port activity 1 LED per channel copper port status
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Switch fault Data link status
Ethernet cabling system	TF switches
Width	74 mm
Height	131 mm
Depth	111 mm
Product weight	0.41 kg

Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	0...95 % without condensation
IP degree of protection	IP20
Standards	EN/IEC 61131-2 UL 1604 Class 1 Division 2 UL 508 CSA C22.2 No 213 Class I Division 2 CSA C22.2 No 214

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1104 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions

