



## Main

Range of product	Modicon TSX Micro automation platform
Product or component type	Analog output module
Number of channels	2
Analogue output type	+/- 10 V 0...20 mA or 4...20 mA

## Complementary

Analogue/Digital conversion	11 bits + sign 0...20 mA or 4...20 mA 11 bits +/- 10 V
Measurement resolution	0...20 mA or 4...20 mA +/- 10 V
Output load	<= 0.6 Ohm 0...20 mA or 4...20 mA >= 1 Ohm +/- 10 V
Protection type	Open-circuit 0...20 mA or 4...20 mA
Temperature drift	0.107 %/10 °C 0...20 mA or 4...20 mA 0.083 %/10 °C +/- 10 V
Current consumption	150 mA
Isolation voltage	1500 V AC
Product weight	0.2 kg

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

## Contractual warranty

Warranty period	18 months
-----------------	-----------