



Main

Product or component type	Socket module
Number of gangs	1 gang
Bulb type	LED blue
Rated current	13 A at 250 V AC 50 Hz

Complementary

Load type	Resistive
Number of cables	3 cable(s) 2.5 mm ² 1 cable(s) 2.5 mm ² 2 cable(s) 2.5 mm ² 1 cable(s) 4 mm ² 2 cable(s) 4 mm ²
Opening distance	> 3 mm
Fixing mode	By screws
Wiring device mounting	Surface Flush
Distance between centers	60.3 mm
Width	87 mm
Height	87 mm
Depth	31.8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
Standards	IEE 16th edition BS 1363-2:1995

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Circularity Profile	No need of specific recycling operations
---------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
