



Overview

Model Name	APC Universal Transfer Switch 6-Circuit 120/240V
Includes	Bypass fast-ons , Hardwire panel , Installation guide , User Manual , Warranty card
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Nominal Output Voltage	120V , 240V
------------------------	-------------

Input

Nominal Input Voltage	120V 240V
Input Frequency	47 - 63 Hz
Input Connections	IEC-320 C14 , NEMA 5-15P , NEMA L14-20P
Number of Power Cords	1
Maximum Line Current per phase	20 A

Physical

Net Weight	9.77 kg
Maximum Height	498.0 mm
Maximum Width	394.0 mm
Maximum Depth	84.0 mm
Shipping Weight	10.91 kg
Shipping Height	533.0 mm
Shipping Width	445.0 mm
Shipping Depth	152.0 mm
Color	Black

Environmental

Operating Environment	-40 - 85 °C
Operating Relative Humidity	5 - 95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Elevation	0-3000 meters
Storage Temperature	-40 - 85 °C
Storage Elevation	0-15000 meters

Conformance

Approvals	cTUVus
Standard warranty	2 years repair or replace
Equipment protection policy	--