

# Product data sheet

Specifications

## Actassi 19-C Patch Panel Sliding Evo 19" 1U 24pt S-One STP Cat6A



VDIG118241BX0

### Main

Range Of Product	Actassi
Product Or Component Type	Equipped sliding 19" data panel
Device Presentation	Loaded
Provided Equipment	4 label holders 24 light grey shutters 24 RJ45 connectors 2 quick fix 19" mountings 1 rear cable organizer
Colour	Dark grey (RAL 7016)
Additional Information	Automatic grounding

### Complementary

Variant	Evolution
Number Of Port	24 port of STP
Communication Network Category	6 <sub>A</sub>
Cover Type	Screened
Mounting Support	19" rack
Number Of Rack Unit	1U
Type Of Connector	S-One
Material	DC01 metal sheet 1.2 mm PA6 plastic part PA66 GF20 plastic part
Width	490 mm
Depth	240 mm
Height	47 mm
Net Weight	2.9 kg

### Environment

Ambient Air Temperature For Operation	-10...55 °C
Standards	IEC 60297 ISO/IEC 11801:ed. 2.2, 2011 NF C 20-150

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.000 cm
Package 1 Width	26.800 cm
Package 1 Length	55.000 cm
Package 1 Weight	3.030 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	18.915 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations