

Product data sheet

Specifications

Actassi 19-C Power Panel 19" 1U 9 x DK 250V 10A Socket-outlets



VDIG161941

Main

Range	Actassi
Product	19" power panel
Provided Equipment	2 quick fix 19" mountings
Colour	Dark grey (RAL 7016)
Additional Features	With personalized cable identification labels

Complementary

Operational Voltage	250 V AC, 10 A
Number Of Socket Outlets	9 Danish socket-outlets conforming to DS/IEC 60884-1
Rack Unit	1U
Marking	CE
Material	PA6 GF30: plastic part Anodised aluminium
Surface Finish	Matt
Depth	47 mm
Height	45 mm
Width	490 mm
Weight	0.9 kg
Targeted Region	Europe

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-10...55 °C
Standards	IEC 60884-1 IEC 60297

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	16.0 cm
Package 1 Length	52.0 cm
Package 1 Weight	1.093 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S04
Number Of Units In Package 2	11
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	12.861 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations