


Product data sheet

Specifications



Actassi 19-C Power Panel 19" 1U 6 x DE 230V 16A Socket-outlets CB RCD

VDIG163631

 **Discontinued on:** Sep 26, 2023

 **Discontinued**

Main

Range	Actassi
Equipment Level	Earth leakage protection With circuit breaker
Product	19" power panel
Provided Equipment	2 quick fix 19" mountings
Colour	Dark grey (RAL 7016)
Additional Features	With personalized cable identification labels

Complementary

Operational Voltage	250 V AC, 16 A, 3680 W
Earth Leakage Current	16 mA, 250 V 30 ms
Number Of Socket Outlets	6 German socket-outlets, 2P + E according to conforming to DIN 49440
Rack Unit	1U
Marking	CE
Material	PA6 GF30: plastic part Anodised aluminium
Depth	86 mm
Height	45 mm
Width	490 mm
Weight	1.1 kg
Targeted Region	Europe

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-10...55 °C
Standards	DIN 49440 IEC 60884-1 IEC 60297

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	17 cm
Package 1 Length	52 cm
Package 1 Weight	1.38 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	11
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	15.975 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations