


Product data sheet

Specifications



Actassi - cover with 6 MTP adapters OS2 - 1U

VDILA36

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Actassi
Product Or Component Type	Cover plate with adapters
Provided Equipment	6 adapters MTP OS2
Quantity Per Set	1
Colour	Cover plate: black (RAL 9005) Adapter: green
Type Of Paint	Cover plate: epoxy

Complementary

Number Of Rack Unit	1U
Product Destination	Overhead support Fibre optic panel
Minimum Number Of Matings	500 cycles
Condition Of Use	Indoor
Fixing Mode	By captive screws
Material	Aluminium alloy: cover plate PEI (polyetherimide): adapter
Targeted Region	Europe
Width	105 mm
Height	37 mm
Depth	14 mm

Environment

Standards	EN 50377-15-1 TIA/EIA-604-5 IEC 61754-7
Ambient Air Temperature For Storage	-25...70 °C
Ambient Air Temperature For Operation	-10...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	19.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	40.0 g