


Product data sheet

Specifications



Actassi - fanout link - SC/MTP - OM3 - 2 mm - Euroclass C

VDILL035D3K2

 **Discontinued on:** Feb 10, 2021

 **Discontinued**

Main

Range	Actassi
Product Or Component Type	Fanout link
Colour	Sheath: aqua SC connector: aqua MTP connector: aqua
Type Of Packing	50...320 m cable drum

Complementary

Product Destination	empty fibre optic patch panel
Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.5 dB 850 nm MTP 0.3 dB 850 nm SC
Minimum Return Loss	20 dB 850 nm MTP 20 dB 850 nm SC
Fibre Performance	OM3
Optic Fiber Diameter	2 mm
Sheath Type	Metallic cylinder
Condition Of Use	Indoor
Cable Outer Diameter	3.8 mm
Material	Plastic: SC connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards

Fibre performance: ITU G.651
Fibre performance: IEC 60793-2-10 Type A1a.2
Cable specification: IEC 60794-2
Cable test procedure: IEC 60794-1-2
Flame retardance: IEC 60332-1
IEC 60754-1
Acidity of combustion gases: IEC 60754-2
Smoke generation: IEC 61034
Performance: ISO/IEC 11801:2011 Ed.2.2
Cabling: ISO/IEC 24764
Fibre cabling test: ISO/IEC 14763-3
TIA/EIA-568-C.3
ANSI/TIA-942
10Gbase-SR: IEEE 802.3ae
SC connector: IEC 61754-4
SC connector: IEC 60874-19
MTP connector: IEC 61754-7
MTP connector: TIA/EIA-604-5