

Product data sheet

Specifications

Actassi - equipped 19" fibre optic panel 48 LC/2x24 MTP - 1U - OM4



VDILP141S5L

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	Actassi
Product Or Component Type	Equipped 19" fibre optic panel
Colour	Panel: black (RAL 9005) MTP adapter: black LC adapter: magenta
Quantity Per Set	1

Complementary

Fibre Performance	OM4
Maximum Insertion Loss	MTP: <0.5 dB at 850 nm LC: <0.3 dB at 850 nm
Minimum Return Loss	20 dB 850 nm MTP 20 dB 850 nm LC
Number Of Rack Unit	1U
Termination 1	24 x LC duplex
Termination 2	2 x 24 MTP
Condition Of Use	Indoor
Type Of Paint	Panel: epoxy
Material	Sheet steel panel PBT (polybutylene terephthalate) LC adapter PEI (polyetherimide) MTP adapter
Device Mounting	Flush
Fixing Mode	Cage nut
Height	44 mm
Width	483 mm
Depth	270 mm
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61754-20 LC adapter IEC 50377-7-x LC adapter IEC 61754-7 MTP adapter EN 50377-15-1 MTP adapter TIA/EIA-604-5 MTP adapter ISO/IEC 11801:2011 Ed.2.2 ISO/IEC 24764 ISO/IEC 14763-3 TIA/EIA-568-C.3 ANSI/TIA-942 IEEE 802.3ae 10Gbase-SR
-----------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	31.0 cm
Package 1 Length	54.0 cm
Package 1 Weight	3.658 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	19.298 kg