

Product data sheet

Specifications



Actassi FL-C Fibre Optic Patchcord - OM2 50/125 2ST-2ST LSZH - 2m

VDIP542112

⚠ Discontinued on: Sep 6, 2019

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Multimode fibre optic patchcord
Colour	Sheath: orange ST housing: metal ST boot: black
Type Of Packing	plastic bag

Complementary

Maximum Attenuation	3 dB at 850 nm 1 dB at 1300 nm
Bandwidth	500 Hz at 1300 nm 500 Hz at 850 nm
Bending Radius	40 mm
Maximum Insertion Loss	0.3 dB
Pulling Force	500 N
Crush Resistance	75000 N/m
Fibre Performance	OM2 50/125 µm
Material	Ceramic: ST connector ferrule
Cable Length	2 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-40...75 °C
Ambient Air Temperature For Installation	-40...75 °C
Ambient Air Temperature For Storage	-40...75 °C
Standards	Fibre performance: IEC 60793-2-10 Type A1a.1 Fibre performance: ITU G.651 Flame retardance: IEC 60332-1 IEC 60754-1 IEC 60754-2 IEC 61034 ST connector: TIA/EIA-604-2 ST connector: IEC 61754-2 Fibre performance: ISO/IEC 11801:2011 Ed.2.2 OM2 Fire retardance: IEC 60332-3C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	13 cm
Package 1 Length	16.5 cm
Package 1 Weight	0.039 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
