

Product data sheet

Specifications



Actassi FL-C Fibre Optic Pigtail OS1/OS2 9/125 LC

VDIP645401

⚠ Discontinued on: Jun 29, 2020

⚠ End-of-service on: Oct 12, 2020

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Singlemode fibre optic pigtail
Colour	Yellow
Type Of Packing	plastic bag

Complementary

Fibre Performance	OS2 9/125 µm
Cable Length	0.7 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-40...75 °C
Ambient Air Temperature For Installation	-40...75 °C
Ambient Air Temperature For Storage	-40...75 °C
Standards	Fibre performance: IEC 60793-2-10 Type A1a.1 Fibre performance: ISO/IEC 11801:2011 Ed.2.2 OM1 LC connector: TIA/EIA-604-10 A IEC 61754-20 Ed.2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	17 cm
Package 1 Length	12 cm
Package 1 Weight	0.006 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)