

Product data sheet

Specifications



LexCom Home Performance - tele connecting cord RJ11/RJ45 UTP - black, 2 m

VDIR542110

⚠ Discontinued on: Aug 31, 2023

⚠ Discontinued

Main

Range	LexCom Home
Product Name	LexCom Home Performance
Product Type	Tele connecting cord

Complementary

Cable Shielding Type	UTP
Cable End 1	1 x RJ11
Cable End 2	1 x RJ45
Insulation Resistance	> 500 MOhm at 100 V DC
Minimum Number Of Matings	500 cycles
Number Of Cables	1 stranded cable(s), AWG 28
Wire Insulation Material	PVC
Colour Tint	Black
Cable Length	2 m

Environment

Standards	AS/ACIF S008 - 2001
-----------	---------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	14.0 cm
Package 1 Length	16.5 cm
Package 1 Weight	33.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.954 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations