

Product data sheet

Specifications



LexCom Home Premium - coaxial splitter kit

VDIR613013

⚠ Discontinued on: Jan 29, 2018

⚠ End-of-service on: Dec 31, 2018

⚠ Discontinued

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	Coaxial splitter kit

Complementary

Kit Composition	2-way coaxial splitter 2 jumper cords
Tv Connector	F connectors
Bandwidth	5...1000 MHz
Maximum Insertion Loss	3.5 dB
Minimum Return Loss	23 dB
Bending Radius	>= 40 mm
Average Impedance	75 Ohm
Insulation Resistance	100 MOhm at 500 V DC
Shield Attenuation	100 dB
Material	Die cast zinc: housing
Fixing Mode	Tap-tite screws
Cable Outer Diameter	0.8 mm
Cable Length	0.5 m 0.3 m
Height	60 mm
Width	55 mm
Depth	20 mm

Environment

Temperature Range	0...40 °C
Standards	EN 50083-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10.5 cm
Package 1 Length	5 cm
Package 1 Weight	0.1 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)