

Product data sheet

Specifications



LexCom Home Premium - TV/R connecting cord - 3 m, black

VDIR643003

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	TV/R connecting cord

Complementary

Connector Type	RJ45
Tv Connector	Female IEC 9.52 mm
Bandwidth	1...862 MHz
Type Of Cable	Quad shielded RG-6/U cable
Maximum Insertion Loss	1.5 dB at 860 MHz
Minimum Return Loss	20 dB 15...200 kHz
Input Impedance	100 Ohm for RJ45 end
Output Impedance	75 Ohm for IEC end
Shield Attenuation	90 dB
Material	PVC (polyvinyl chloride)
Wire Insulation Material	PE
Signal Velocity	0.83
Load Capacitance	53.2 pF/ 3 m
Colour Tint	Black (RAL 9005)
Cable Outer Diameter	1.02 mm
Cable Length	3 m
Weight	0.23 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	325.0 g
Unit Type Of Package 2	S03

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)