


Product data sheet

Specifications



LexCom Home Premium - XR110 radio connecting cord - black, 3 m

VDIR643005

 **Discontinued on:** Dec 31, 2018

 **Discontinued**

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	Radio connecting cord
Commercial Name	XR110

Complementary

Connector Type	RJ45
Radio Connector	Female IEC 9.52 mm
Bandwidth	85...110 MHz
Minimum Filter Selectivity Attenuation	20 dB
Type Of Cable	Double shielded coaxial cable
Maximum Insertion Loss	1 dB at 100 MHz
Minimum Return Loss	10 dB
Input Impedance	100 Ohm for RJ45 end
Output Impedance	75 Ohm for IEC end
Material	PVC (polyvinyl chloride)
Colour Tint	Black (RAL 9005)
Cable Outer Diameter	5.8 mm
Cable Length	3 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	20 cm
Package 1 Length	16 cm
Package 1 Weight	0.157 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)