

Product data sheet

Specifications



LexCom Home Premium - C110-2 AV combiner

VDIR673004

⚠ Discontinued on: Dec 31, 2016

⚠ Discontinued

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	AV combiner
Commercial Name	C110-2

Complementary

Connector Type	1 port(s) RJ45 - cable shielding type: U/FTP for output 2 port(s) RJ45 - cable shielding type: U/FTP for input
Bandwidth	80...862 MHz
Maximum Insertion Loss	8 dB 6.5 dB
Transmission Frequency	470 MHz 862 MHz
Minimum Return Loss	10 dB
Input Impedance	100 Ohm
Output Impedance	100 Ohm
Shield Attenuation	65 dB
Minimum Number Of Matings	500 cycles
Contacts Material	Plated 3 µm Sn over 20 µm Cu
Material	PC/ABS: housing
Height	37 mm
Width	86 mm
Depth	72 mm
Weight	0.11 kg

Environment

Temperature Range	0...40 °C
Ambient Air Temperature For Storage	-20...60 °C

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications