



Main

Range of product	Actassi
Product name	Actassi ON
Product or component type	Manager panel
Colour tint	Dark grey (RAL 7016)

Complementary

Number of rack unit	1U
Device composition	power supply 3 bus connector 2 bus termination
Product destination	Manage the patch panels
Display type	LCD screen status and alert
Connector type	Front: bus Front: LAN Rear: rack lamp output Rear: power input
[Us] rated supply voltage	100...240 V AC 50/60 Hz, <1.5 A
Material	1.5 mm sheet metal
Material	Europe

Environment

Ambient air temperature for operation	0...40 °C
Standards	IEC 60320

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
