



### Main

Range	Base
Product or component type	Switch
Device presentation	Mechanism
Colour tint	White
Type of packing	Group

### Complementary

Switch function	1-way
Local signalling	Without pilot light
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Material	ABS + PC
Number of modules	1
Depth	38.35 mm
Height	25 mm
Width	45 mm
Connections - terminals	Screw-clamp terminals
Cable cross section	4 mm <sup>2</sup>
AWG gauge	AWG 12
Fixing mode	Clip-in

### Environment

Standards	NM 60669-1
-----------	------------

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations