



Main

Range	Base
Product or component type	Dimmer + switch
Device presentation	Flush-mounting module
Colour tint	White
Type of packing	Bag

Complementary

Dimmer application	Fan
Switch function	1-way
[Ue] rated operational voltage	250 V AC
Rated power in W	400 W
Material	ABS + PC
Depth	39 mm
Height	45 mm
Width	25 mm
Connections - terminals	Pre-stripped wire terminations
Cable cross section	1.5 mm ²
AWG gauge	AWG 14
Fixing mode	Clip-in

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.