



### Main

Range of product	Exxact
Product or component type	Light signal
Provided equipment	6 pre-printed films

### Complementary

Wiring device mounting	Flush
Rated supply voltage	120...230 V AC 60 Hz 1.6 W 150...230 V AC 50 Hz 1.3 W
Local signalling	Lamp
Light source	LED
Light source colour	White
Colour	White
Material	Polycarbonate brilliant Metal/plastic for insert

### Environment

IP degree of protection	IP20
Environmental health and issues	Halogen free

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---