



Main

Range of product	Exxact
Range	Exxact
Product or component type	Socket-outlet
Cover type	Without lid
Device presentation	Complete product

Complementary

Device mounting	Surface
Socket number	1
Outlet poles configuration	2P + E with shutters
Rated current/voltage	16 A - 250 V AC
Colour	White RAL 9003
Connections - terminals	Screwless terminals
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² solid cable(s) 1 x 1.5...2 x 2.5 mm ² solid stranded cable(s)
Material	PC PC (polycarbonate)
Height	65 mm
Width	65 mm
Projecting depth	42 mm

Environment

Standards	IEC 60884-1 SFS 5610:2004 SS 4280834
Product certifications	FIMKO SEMKO
IP degree of protection	IP21

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1808 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations