



Main

Range of product	Exxact
Product or component type	Basic movement detector
Quantity per set	1 piece

Complementary

Version	Basic version
Rated power in W	350 W
Wiring device mounting	Flush
Power range	40...350 W incandescent lamp 40...350 W 230 V AC halogen lamp
Detection angle	120°
Light sensitivity	0...500 lux
Time delay	1 s...20 min
Rated current/voltage	16 A - 230 V AC
Colour	Anthracite
Connections - terminals	Screwless terminals
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² solid cable(s) 1 x 1.5...2 x 2.5 mm ² solid stranded cable(s)
Material	ABS (acrylonitrile butadiene-styrene)
Wiring configuration	Without neutral
Mounting height	1...1.5 m
Embedding depth	16 mm
Height	71 mm
Width	71 mm
Projecting depth	20 mm
Product compatibility	To be completed with Exxact frame

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	EN 60669-2-1 EN 61000-6
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------