



Main

Range	Exxact
Product or component type	Thermostat
Device application	Temperature control
Colour	Anthracite
Quantity per set	Set of 1

Complementary

[Ue] rated operational voltage	24 V AC 50 Hz
[In] rated current	4 A (resistive load)
Rated current/voltage	4 A - 24 V AC
Power consumption in VA	240 VA
Product compatibility	To be completed with Exxact frame design
Contacts type and composition	1 C/O
Switch function	1-pole
Connections - terminals	Screw terminals
Temperature setting range	5...30 °C
Material	ABS (acrylonitrile butadiene-styrene)
Device mounting	Flush
Height	71 mm
Width	71 mm
Embedding depth	25 mm
Projecting depth	16 mm

Environment

IP degree of protection	(IP20) also with visual parts removed
Standards	EN 60669-1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------