



### Main

Range	Exxact
Product or component type	Rocker switch
Quantity per set	Set of 5

### Complementary

Device presentation	Mechanism
Switch function	2-pole + 1-pole
Switch pattern	[2+1]
Rated current/voltage	16 A - 250 V - AC
Colour	Metallic
Connections - terminals	Screwless terminals
Loop terminals	1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> solid stranded cable(s)
Optional fixing mode	By claw kit insert By screw rocker
Embedding depth	15 mm
Height	71 mm
Width	71 mm
Projecting depth	18 mm

### Environment

Standards	EN 60669-1
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed) IP44 (with additional sealing kit)

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1842 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---------------------------------------------------------------------------------------------------------------------------------------

---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--------------------------------------------------------------------------------------------------------

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---