



### Main

Range	Exxact
Range of product	Exxact
Product or component type	Dimmer

### Complementary

Dimmer type	Transistor
Dimmer control	Rotary push type
Control type	Rotary push type
Switch function	1-pole 2-way
Load type	Incandescent lamp : Halogen lamp : @230 V Electronic transformer :
Power range	Incandescent lamp : 40...315 W Halogen lamp : 40...300 W Electronic transformer : 40...315 W
Rated current/voltage	10 A - 230 V AC
Protection type	Short-circuit and overload protection with automatic reset
Connections - terminals	Screw terminals
Number of loop terminals	1
Shape of screw head	Pozidriv No 1 and combi
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> solid stranded cable(s)
Colour	Metallic
Material	ABS (acrylonitrile butadiene-styrene)
Device mounting	Flush
Embedding depth	29 mm
Height	71 mm
Width	71 mm
Projecting depth	22 mm
Product compatibility	LED illumination light kit

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 60669-1 EN 60669-2-1
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed) IP44 (with additional sealing kit)

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------