



Main

Range of product	Exxact
Range	Exxact
Product or component type	Socket-outlet
Device presentation	Mechanism
Quantity per set	5 pieces

Complementary

Device mounting	Flush
Socket number	3
Outlet poles configuration	2P with shutters
Rated current/voltage	2.5 A - 250 V AC
Colour	Metallic
Connections - terminals	Screw terminals
Number of loop terminals	2
Shape of screw head	Pozidriv No 1 and combi
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² solid cable(s) 1 x 1.5...2 x 2.5 mm ² solid stranded cable(s)
Material	ASA + PC
Embedding depth	29 mm
Height	70.8 mm
Width	70.8 mm
Projecting depth	11.8 mm

Environment

Standards	IEC 60884-1 SFS 5610:2004 SS 4280834 IEC 60884-2-2 NEK 502:2006
Product certifications	FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed)

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1808 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
