



Main

Range	Exxact
Range of product	Exxact
Product or component type	Dimmer

Complementary

Dimmer type	Universal
Dimmer control	Rotary push type
Control type	Rotary push type
Switch function	1-pole 2-way
Load type	Incandescent lamp : Halogen lamp : @230 V Conventional transformer : Electronic transformer :
Power range	Incandescent lamp : 40...420 W Halogen lamp : 40...420 W Electronic transformer : 40...420 W Conventional transformer : 40...420 W
Rated current/voltage	10 A - 230 V AC
Protection type	Electronic short-circuit and automatic overload protection
Connections - terminals	Screw terminals
Number of loop terminals	1
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² solid cable(s) 1 x 1.5...2 x 2.5 mm ² solid stranded cable(s)
Colour	Metallic
Material	ABS (acrylonitrile butadiene-styrene)
Device mounting	Flush
Embedding depth	29 mm
Height	71 mm
Width	71 mm
Projecting depth	22 mm
Product compatibility	LED illumination light kit

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	EN 60669-1 EN 60669-2-1
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed) IP44 (with additional sealing kit)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------