



### Main

Range	Exxact
Product or component type	DCL plug
Mounting mode	On luminaire cord
Colour tint	White
Quantity per set	Set of 25

### Complementary

Outlet poles configuration	2P + E
[In] rated current	6 A
Rated voltage	250 V AC
Material	PC/ABS
Connections - terminals	Screw terminal
Clamping connection capacity	3 x 0.75 mm <sup>2</sup> for flexible cable(s)
Height	17 mm
Width	29 mm
Length	32 mm

### Environment

IP degree of protection	IP20
Standards	NEK EN61995-1 NEK EN61995-2
Product certifications	NEMKO

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1820 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---