



Main

Range	Exxact
Product or component type	Rocker switch
Quantity per set	Set of 1

Complementary

Device presentation	Complete switch
Switch function	Double 2-way
Switch pattern	[6+6]
Rated current/voltage	16 A - 250 V - AC
Colour	Anthracite
Connections - terminals	Screw terminals
Loop terminals	2
Shape of screw head	Pozidriv No 1 and combi
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² solid cable(s) 1 x 1.5...2 x 2.5 mm ² solid stranded cable(s)
Optional fixing mode	By claw kit insert
Embedding depth	15 mm
Height	87 mm
Width	87 mm
Projecting depth	18 mm

Environment

Standards	EN 60669-1
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed)

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1842 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
