



### Main

Range	Exxact
Product or component type	Rocker switch
Quantity per set	Set of 1

### Complementary

Device presentation	Complete switch
Switch function	2-circuits
Switch pattern	[5]
Rated current/voltage	16 A - 250 V - AC
Colour	Brushed steel
Connections - terminals	Screw terminals
Loop terminals	2
Shape of screw head	Pozidriv No 1 and combi
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> solid stranded cable(s)
Optional fixing mode	By claw kit insert
Embedding depth	15 mm
Height	87 mm
Width	87 mm
Projecting depth	18 mm

### Environment

Standards	EN 60669-1
Product certifications	CE FIMKO NEMKO SEMKO
IP degree of protection	IP20 (also with visual parts removed)

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1808 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---