

Product data sheet

Specifications



booted head for pushbutton XAC-B -
white - 4 mm, -40..+70 °C

XACB9121

Main

| | |
|---------------------------------|--|
| Range Of Product | Harmony XAC |
| Product Or Component Type | Head for push-button |
| Component Name | XACB |
| Marking | Unmarked |
| Operator Additional Information | Booted |
| Operating Travel | 4 mm |
| Cap/Operator Or Lens Colour | White |
| Product Compatibility | XENB.... XESD2251 XESD2241 XEND.... XESB2011 XENC.... XESD2201 |
| Sale Per Indivisible Quantity | 10 |

Complementary

| | |
|------------|----------|
| Net Weight | 0.005 kg |
|------------|----------|

Environment

| | |
|---------------------------------------|--|
| Standards | IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1 |
| Ambient Air Temperature For Operation | -40...70 °C |
| Ambient Air Temperature For Storage | -40...70 °C |
| Vibration Resistance | 15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6 |
| Shock Resistance | 100 gn conforming to IEC 60068-2-27 |
| Electrical Shock Protection Class | Class II conforming to IEC 61140 |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 11.5 cm |
| Package 1 Width | 2.7 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|---------|
| Package 1 Length | 10.0 cm |
| Package 1 Weight | 6.0 g |
| Unit Type Of Package 2 | BAG |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 11.5 cm |
| Package 2 Width | 2.7 cm |
| Package 2 Length | 10.0 cm |
| Package 2 Weight | 61.0 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|--|
|  Reach Free Of Svhc | |
|  Toxic Heavy Metal Free | |
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |