



Main

Range of product	OsiSense XC
Series name	Standard format
Device short name	XCKM
Material	Metal
Body material	Zamak
Fixing mode	By the body
Movement of operating head	Linear Rotary
Number of poles	2
Contacts type and composition	1 NC + 1 NO

Complementary

Switch actuation	By 30° cam
Contacts insulation form	Zb
Number of steps	1
Positive opening	With
Positive opening minimum torque	0.25 N.m
Minimum force for tripping	8 N
Maximum actuation speed	1.5 m/s
Width	64 mm
Height	64 mm
Depth	30 mm

Environment

Ambient air temperature for operation	-25...70 °C
Standards	-

Contractual warranty

Warranty period	18 months
-----------------	-----------

XCKM221 is replaced by:



Classic range XCKM121

limit switch XCKM - thermoplastic roller lever plunger - 1NC+1NO - snap - Pg11

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 1999
