

Product data sheet

Specifications



split sprocket with through hub -
12.7 mm pitch - 24 teeth - shaft Ø
80

XR2AZ52450

⚠ Discontinued on: Jan 12, 2022

⚠ Discontinued

Main

Range Of Product	XR
Accessory / Separate Part Designation	Split sprocket with through hub
Accessory / Separate Part Type	Winch shaft chain sprocket
Accessory / Separate Part Category	Separate parts
Accessory / Separate Part Destination	Screw limit switch

Complementary

Number Of Teeth	24
Chain Pitch	12.7 mm
Bore Diameter For Shaft	21...50 mm
Shaft Diameter	80 mm
External Diameter	105 mm
Pinion Length	60 mm

Environment

Standards	NF E 23-111
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications