



## Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS5
Sensor design	Form 8 x 43 x 8
Size	8 mm
Body type	Fixed
Enclosure material	Nickel plated brass
Type of output signal	Discrete
Wiring technique	3-wire
[Sn] nominal sensing distance	15 mm
Discrete output function	1 NO
Discrete output type	PNP
Electrical connection	Cable
Cable length	2 m
[Us] rated supply voltage	12...24 V DC
Switching capacity in mA	<= 200 mA
IP degree of protection	IP67

## Complementary

Detection face	Lateral top
Detector flush mounting acceptance	Flush mountable
Material	Metal
Front material	PPS
Output circuit type	DC
Cable composition	3 x 0.11 mm <sup>2</sup>
Wire insulation material	PVC
Switching frequency	<= 2500 Hz
Marking	CE
Depth	8 mm

---

Height	8 mm
Width	43 mm

---

### Environment

---

Product certifications	UL
Ambient air temperature for operation	-40...70 °C

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---