



## Main

Range of product	OsiSense XU
Sensor name	XUY
Sensor design	Fiber design
Sheath type	Standard
[Sn] nominal sensing distance	200 mm XUYAFV
End fitting type	Straight with nickel plated brass, M4 x 0.7

## Complementary

Electronic sensor type	Photo-electric sensor
Optic fiber material	50 $\mu$ glass
Sheath material	PVC + thermo polyolefine
Detection system	Thru beam
Optic fiber length	1 m
Minimum bending radius	10 mm
Head mounting	M4 x 0.7
Net weight	0.042 kg

## Environment

Ambient air temperature for operation	-25...60 °C
---------------------------------------	-------------

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------