



Main

Range of product	OsiSense XU
Product or component type	Ring light
Accessory / separate part category	Lighting accessory
Light source	LED white

Complementary

Material	Aluminium box PMMA (polymethyl methacrylate) front face
Product compatibility	XUW
Product weight	0.15 kg
[Us] rated supply voltage	24 V DC with reverse polarity protection
Supply voltage limits	21...26 V DC
Current consumption	<= 390 mA (no-load)
Electrical connection	2 male connectors M12 12 pins
Input type	Trigger mode

Environment

Product certifications	CE
Ambient air temperature for operation	0...50 °C
Ambient air temperature for storage	-20...60 °C
IP degree of protection	IP65 conforming to IEC 60529

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--