



ⓘ Discontinued

XVPC6M8W has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Harmony XVP Universal
Product or component type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit with cream clamping ring
Signalling type	Flashing
Mounting diameter	50 mm
Component name	XVPC
Material	Polycarbonate and polyamide
Light source	Yellow integral flash discharge tube
Bulb type	Flash discharge tube
[Us] rated supply voltage	230 V AC
Flash energy	0.6 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals : $\leq 1 \times 1.5 \text{ mm}^2$ with cable end
Marking	CE
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current consumption	$\leq 11 \text{ mA AC}$
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Flashing frequency	0.6...2 Hz
Service life in hours	> 1000 h (-25...50 °C)
CAD overall width	56 mm
CAD overall height	65 mm
CAD overall depth	56 mm
Product weight	0.115 kg

Environment

Product certifications	cULus
Standards	EN/IEC 60947-5-1
Protective treatment	TC

Ambient air temperature for storage	-40...70 °C
Electrical shock protection class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529


Contractual warranty

Warranty period	18 months
-----------------	-----------

Indicator Bank without Audible Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



Number of illuminated units	b in mm	b in in.
1	108	4.25
2	170	6.69
3	232	9.13
4	294	11.57
5	356	14.02