



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product compatibility	XC2J
Associated lever	ZC2JY11 ZC2JY12 ZC2JY13 ZC2JY31 ZC2JY51 ZC2JY81 ZC2JY91
Associated body	ZC2JC46 ZC2JD46
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach 1 direction

Complementary

Switch actuation	CW From left
Positive opening	Without
Product weight	0.21 kg
Head material	Metal

Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-40...70 °C

Environmental characteristic	Low temperature
------------------------------	-----------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
