



Main

| | |
|----------------------------|--|
| Range of product | OsiSense XC |
| Series name | Special format |
| Product or component type | Limit switch head |
| Device short name | ZC2J |
| Head type | Plunger head |
| Product compatibility | XC2J |
| Associated body | ZC2JC16 ZC2JC26 ZC2JD16 ZC2JD26 |
| Movement of operating head | Linear |
| Type of operator | Side plunger spring return metal |
| Type of approach | Lateral approach 1 direction |

Complementary

| | |
|------------------|---------|
| Switch actuation | On end |
| Positive opening | Without |
| Product weight | 0.24 kg |
| Head material | Metal |

Environment

| | |
|---------------------------------------|-----------------|
| Ambient air temperature for operation | -40...70 °C |
| Ambient air temperature for storage | -40...70 °C |
| Environmental characteristic | Low temperature |

Offer Sustainability

| | |
|----------------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
