



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Plunger head
Product compatibility	XC2J
Associated body	ZC2JC15 ZC2JC25
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with horizontal roller)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	Without
Product weight	0.245 kg
Head material	Metal

Environment

Ambient air temperature for operation	10...120 °C
Ambient air temperature for storage	10...120 °C
Environmental characteristic	High temperature

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
