



Main

| | |
|----------------------------|---|
| Range of product | OsiSense XC |
| Series name | Special format |
| Product or component type | Limit switch head |
| Device short name | ZC2J |
| Head type | Plunger head |
| Product compatibility | XC2J |
| Associated body | ZC2JC15 ZC2JC25 |
| Movement of operating head | Linear |
| Type of operator | Roller plunger spring return metal (ball bearing mounted) |
| Type of approach | Multi-directional approach |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without |
| Product weight | 0.205 kg |
| Head material | Metal |

Environment

| | |
|---------------------------------------|------------------|
| Ambient air temperature for operation | 10...120 °C |
| Ambient air temperature for storage | 10...120 °C |
| Environmental characteristic | High temperature |

Offer Sustainability

| | |
|----------------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
