



## Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Plunger head
Product compatibility	XC2J
Associated body	ZC2JC4 ZC2JC48 ZC2JD4
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with vertical roller)
Type of approach	Vertical approach 2 directions

## Complementary

Switch actuation	By 30° cam
Positive opening	Without
Product weight	0.245 kg
Head material	Metal

## Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant

 Schneider Electric declaration of conformity

---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---