



## Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE01 ZC2JE02 ZC2JE03 ZC2JE04 ZC2JE05 ZC2JE06 ZC2JE07
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (offset)
Type of approach	Lateral approach

## Complementary

Switch actuation	By 30° cam
Positive opening	Without

## Environment

Ambient air temperature for operation	10...120 °C for high temperature
Ambient air temperature for storage	10...120 °C for high temperature
Environmental characteristic	High temperature

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---