



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKT XCKD XCKP
Associated body	ZCP26 ZCMD29L5 ZCMD37L2 ZCP21 ZCP27 ZCP29 ZCD37 ZCMD37L5 ZCMD29L2 ZCP35 ZCD39 ZCMD41L1 ZCD26 ZCMD21L1 ZCD28 ZCT28P16 ZCMD39L2 ZCT27N12 ZCMD41L2 ZCMD61C12 ZCMD39L1 ZCMD21L08U78 ZCT28G11 ZCD21M12 ZCD35 ZCT26N12 ZCP31 ZCT25G11

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCD31
 ZCT21P16
 ZCT27P16
 ZCT27G11
 ZCMD21M12
 ZCT28N12
 ZCP29M12
 ZCMD81L5
 ZCMD41L5
 ZCMD21C12
 ZCT25N12
 ZCP37
 ZCT25P16
 ZCMD25L2
 ZCMD21L08R12
 ZCP28
 ZCMD29L1
 ZCMD25L1
 ZCP25
 ZCT21G11
 ZCMD81L1
 ZCD29
 ZCMD81L2
 ZCT26G11
 ZCP21M12
 ZCMD37L1
 ZCMD21L5
 ZCMD25L5
 ZCP39
 ZCD29M12
 ZCMD69C12
 ZCMD29C12
 ZCT21N12
 ZCD25
 ZCD21
 ZCT26P16
 ZCMD21L2
 ZCD27
 ZCMD39L5
 ZCMD61M12

Movement of operating head	Linear
Type of operator	Roller plunger spring return metal (with silicone boot)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------